PRODUCT INFORMATION

STORA

2370PIP100S74

EAN 4031582369359

Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Stora
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	80 kg
Electric Conductive	No
Stainless	No
Load capacity Static	160 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	128 mm

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Slim
Swivel Bearing	Two ball races
Offset	35 mm
Swivel radius	85 mm
Swivel interference	170 mm

WHEEL

Tread hardness	soft
Body material	Polypropylene
Tread Material Mix	Solid rubber, non-marking
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	100 mm
Tread width	32 mm
Hardness of tread (A)	75 Shore A

FITTING

Fitting type	Threaded stem with hexagon neck, top, riveted

© Copyright 2026 TENTE International GmbH