PRODUCT INFORMATION

KAPPA LOAD

9651TOO250P63

EAN 4031582314649



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●●
Movement Noise	●○○○○
Attrition	●●●●●
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Kappa load
Type	Swivel castor with directional lock
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	1320 kg
Load capacity at 6 km/h	1100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	2640 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall Height	305 mm
Overall weight	5.34 kg

HOUSING

Housing Material	Iron forged, heavy
Fork shape	Broad, reinforced
Swivel Bearing	Deep-groove ball thrust roller bearing
Offset	61 mm
Swivel interference	398 mm
Lubrication nipple	1

WHEEL

Body material	Polyamide, heavy
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	250 mm
Tread width	50 mm
Hardness of tread (D)	75 Shore D

FITTING

Fitting type	Medium rectangular plate
Plate length	135 mm
Plate width	110 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

© Copyright 2026 TENTE International GmbH


KAPPA LOAD


9651TOO250P63


EAN 4031582314649


Order number 00830361

Product Drawings









© Copyright 2026 TENTE International GmbH