PRODUCT INFORMATION

AGILA STAINLESS

7478PJC125P50

EAN 4031582350029



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●●○
Attrition	●●●○○
Corrosion Resistance	●●●●●

CORE ATTRIBUTES

Product Name	Agila stainless
Type	Fixed castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Electric Conductive	No
Stainless	Yes
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	160 mm
Overall width	60 mm
Overall weight	0.64 kg

HOUSING

Housing Material	Stainless steel, medium
Fork shape	Broad
Housing Color	Stainless steel
Dome diameter	60 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Precision ball bearing, stainless
Wheel Color	Silver grey (RAL7001)
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Body width	32 mm
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	77 mm
Plate width	67 mm
Plate hole length (Minimum)	46.5 mm
Plate hole length (Maximum)	51.5 mm
Plate hole width (Minimum)	56 mm
Plate hole width (Maximum)	61.5 mm
Plate hole diameter	8.5 mm
Hint	Longside of plate 90° off track.

© Copyright 2026 TENTE International GmbH


AGILA STAINLESS


7478PJC125P50


EAN 4031582350029

Order number 00037233

Product Drawings







© Copyright 2026 TENTE International GmbH