

# MAXTECH

UAP160X40-Ø20 HL60 RED

EAN 4031582322989



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	6.3 in
Tread width	1.57 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Hardness of tread (D)	60 Shore D

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	771.62 lb
Load capacity at 3.7 mph	661.39 lb
Load capacity Static	1543.23 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	1.71 lb

# MAXTECH

UAP160X40-Ø20 HL60 RED

EAN 4031582322989



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

