

# STYLEA

5920UAI055L51-10 DOM18 RAL9011

EAN 4031582443240



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                             |
|-----------------------------|-----------------------------|
| Product name                | Stylea                      |
| Housing type                | Swivel castor               |
| Standard                    | EN12528 - Furniture Castors |
| Load capacity at 3 km/h     | 40 kg                       |
| Load capacity Static        | 80 kg                       |
| Temperature range (Minimum) | -10 °C                      |
| Temperature range (Maximum) | 40 °C                       |
| Overall height              | 57 mm                       |
| Overall width               | 37 mm                       |
| Overall weight              | 0.65 kg                     |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polyamide                      |
| Tread material        | Polyurethane, injected         |
| Bearing               | Plain bearing with spacer tube |
| Axle                  | Riveted                        |
| Threadguards          | Without threadguard            |
| Diameter              | 55 mm                          |
| Tread width           | 11 mm                          |
| Hardness of tread (A) | 92 Shore A                     |

## HOUSING

|                     |                    |
|---------------------|--------------------|
| Material fork       | Polyamide          |
| Fork shape          | Twin wheel housing |
| Swivel bearing      | Stem, swiveling    |
| Swivel radius       | 47 mm              |
| Swivel interference | 94 mm              |
| Dome diameter       | 18 mm              |

## FITTING

|                    |                            |
|--------------------|----------------------------|
| Fitting type       | Blind hole for B10 fitting |
| Bolt hole diameter | 10 mm                      |

# STYLEA

5920UAI055L51-10 DOM18 RAL9011

EAN 4031582443240



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

