PRODUCT INFORMATION

# AGILA STAINLESS

7477PJC075P30-11

EAN 4031582351316



Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement Noise | ●●●●○ |
| Attrition | ●●●○○ |
| Corrosion Resistance | ●●●●● |

## CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Agila stainless |
| Type | Swivel castor with total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 75 kg |
| Electric Conductive | No |
| Stainless | Yes |
| Load capacity Static | 150 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall Height | 100 mm |
| Overall width | 43 mm |
| Overall weight | 0.32 kg |

## HOUSING

| | |
|---|---|
| Housing Material | Stainless steel, medium |
| Fork shape | Broad |
| Swivel Bearing | Two ball races |
| Housing Color | Stainless steel |
| Offset | 24 mm |
| Swivel radius | 81 mm |
| Swivel interference | 162 mm |
| Material spring | highly corrosion-resistant zinc flake coating |
| Material brake pedal | chrome-plated zinc-die-casting |
| Dome diameter | 43 mm |

## WHEEL

| | |
|---|---|
| Body material | Polypropylene |
| Tread Material Mix | Thermoplastic rubber |
| Bearing | Precision ball bearing, stainless |
| Wheel Color | Silver grey (RAL7001) |
| Threadguards | With threadguard |
| Diameter | 75 mm |
| Tread width | 25 mm |
| Body width | 25 mm |
| Hardness of tread (A) | 87 Shore A |

## FITTING

| | |
|---|---|
| Fitting type | Bolt hole |
| Bolt hole diameter | 11 mm |
| Hint | Castors can be mounted with standard screws of any length. |

© Copyright 2026 TENTE International GmbH


# AGILA STAINLESS


7477PJC075P30-11

EAN 4031582351316

Order number 00037780

**Product Drawings**



© Copyright 2026 TENTE International GmbH