

NOVATECH

ITP 100x40-Ø15 HL40 cv

EAN 4031582383867



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE


Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	300 kg
Nosivost na 6 km/h	240 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	600 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0.46 kg

TOCAK

Tread profile	konveksan
Materijal za telo	Aluminijum
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	40 mm
dimenzija rupa osovina	15 mm
dužina glavčine	40 mm
Širina tela	40 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D
Pogodno za	pimespo_still_wagner




NOVATECH

ITP 100x40-015 HL40 cv

EAN 4031582383967

Broj porudžbine 00830212



BETTER MOBILITY. BETTER LIFE.