

KAPPA

9680IEP300P63 CL67

EAN 4031582348644
Order number 00838184



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Kappa
Type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1322.77 lb
Load capacity at 3.7 mph	1058.22 lb
Load capacity Static	2645.54 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall height	13.98 in
Overall width	4.33 in
Overall weight	16.03 lb

WHEEL

Body material	Aluminum
	soft
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Jet black (similar RAL9005)
Threadguards	Without threadguard
Diameter	11.81 in
Tread width	2.17 in
Body width	2.17 in
Hardness of tread (A)	68 Shore A

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Color	Blue passivated
Offset	2.76 in
Swivel radius	8.76 in
Swivel interference	17.52 in
	✓
Dome diameter	4.37 in

FITTING

Fitting type	Rectangular plate
Plate length	5.31 in
Plate width	4.33 in
Plate hole length (Minimum)	2.95 in
Plate hole length (Maximum)	3.15 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.43 in

KAPPA

9680IEP300P63 CL67

EAN 4031582348644
Order number 00838184



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

