

# MAXTECH EVO

PBO200X48-Ø12 HL35 TFR

EAN 4031582400380



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Polyurethane, biosourced, injected
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	200 mm
Tread width	48 mm
Axle hole diameter	12 mm
Hub length	34 mm

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Maxtech evo
Housing type	Wheel
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Overall weight	0.35 kg

# MAXTECH EVO

PBO200X48-Ø12 HL35 TFR

EAN 4031582400380



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

