

PRODUCT INFORMATION

BASETECH

POR125x40-Ø12 HL48 natur

EAN 4031582410419



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement noise	● ● ● ● ○ ○
Attrition	● ● ● ● ● ●
Corrosion resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Basetech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	440.92 lb
Electric conductive	no
Stainless	no
Load capacity Static	881.85 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.45 lb



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.57 in
Axle hole diameter	0.47 in
Hub length	1.89 in
Hardness of tread (D)	65 Shore D

BASETECH

POR125x40-Ø12 HL48 natur

EAN 4031582410419



BETTER MOBILITY. BETTER LIFE.

Product Drawings

