

# ELASTECH

UFP100X34-Ø8

EAN 4031582338690  
Order number 00031810



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	3.94 in
Tread width	1.34 in
Axle hole diameter	0.33 in
Hub length	1.77 in
Hardness of tread (A)	63 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	352.74 lb
Load capacity Static	705.48 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	0.65 lb

# ELASTECH

UFP100X34-Ø8

EAN 4031582338690  
Order number 00031810



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

