PRODUCT INFORMATION

DURATECH HEAT

WOO075x25-Ø8 HL31

EAN 4031582367362

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Thermoplastic synthetics, heat resistant
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	75 mm
Tread width	25 mm
Axle Hole Diameter	8 mm
Hub Length	31 mm

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●●●
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Duratech heat
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	75 kg
Electric Conductive	No
Stainless	No
Load capacity Static	150 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	200 °C

© Copyright 2026 TENTE International GmbH


DURATECH HEAT

WOO075x25-Ø8 HL31

EAN 4031582367362

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH