

# COMPACTA

1438PVH050P60-67X48

EAN 3700001796748



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Compacta
Housing type	Fixed castor
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	88.18 lb
Load capacity Static	176.37 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	2.56 in
Overall weight	0.32 lb

## WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Plain bearing
Axle	Riveted
Threadguards	With threadguard
Diameter	1.97 in
Tread width	0.83 in
Hardness of tread (A)	85 Shore A

## HOUSING

Material	Steel sheet, light
Fork shape	Broad

## FITTING

Fitting type	Rectangular plate
Plate length	2.64 in
Plate width	1.89 in
Plate hole length (Maximum)	2.17 in
Plate hole width (Maximum)	1.18 in
Plate hole diameter	0.24 in