

COMPACTA

1438PVH050P60-67X48

EAN 3700001796748



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Compacta
Type	Fixed castor
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	88.18 lb
Load capacity Static	176.37 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	2.56 in
Overall weight	0.32 lb

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Plain bearing
Axle	Riveted
Threadguards	With threadguard
Diameter	1.97 in
Tread width	0.83 in
Hardness of tread (A)	85 Shore A

HOUSING

Material	Steel sheet, light
Fork shape	Broad

FITTING

Fitting type	Rectangular plate
Plate length	2.64 in
Plate width	1.89 in
Plate hole length (Maximum)	2.17 in
Plate hole width (Maximum)	1.18 in
Plate hole diameter	0.24 in