

# PURETECH

PIR 160x40-Ø20

EAN 4031582320374



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja	● ● ● ● ○ ○
Buka u pokretu	● ● ● ● ○
Ishrana	● ● ● ● ○ ○
otpornost na rdju	● ● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	135 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	270 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0.85 kg

## TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma, bez obeležavanja
Nošenje	kotrljajuci lezaj
Boja Tocak	Grafitna crna (RAL9011)
štيتnici omotaca	Bez stražara
Prečnik	160 mm
Širina omotac	40 mm
dimenzija rupa osovina	20 mm
dužina glavnice	58 mm
Širina tela	40 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

# PURETECH

PIR 160x40-Ø20

EAN 4031582320374

Broj porudžbine 00023493  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

