

PURETECH

PIP150X32-Ø8

EAN 4031582356694
Order number 00038560



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread hardness	soft
Tread material	Solid rubber, non-marking
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	150 mm
Tread width	32 mm
Axle hole diameter	8 mm
Hub length	36.5 mm
Hardness of tread (A)	75 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	80 kg
Load capacity Static	160 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.43 kg

PURETECH

PIP150X32-Ø8

EAN 4031582356694
Order number 00038560



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

