

ALPHA

3478UOJ160P63

EAN 4031582307085
Order number 00027861



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Alpha |
| Type | Fixed castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 350 kg |
| Load capacity Static | 700 kg |
| Temperature range (Minimum) | -25 °C |
| Temperature range (Maximum) | 80 °C |
| Overall height | 200 mm |
| Overall width | 115 mm |
| Overall weight | 1.548 kg |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide |
| Tread material | Identical with wheel body |
| Bearing | Roller bearing |
| Axle | Screwed with nut |
| Wheel color | Natural white |
| Threadguards | With threadguard |
| Diameter | 160 mm |
| Tread width | 40 mm |
| Body width | 40 mm |
| Hardness of tread (D) | 75 Shore D |

HOUSING

| | |
|---------------|--------------------|
| Material fork | Steel sheet, heavy |
| Fork shape | Broad |
| Colour | Blue passivated |

FITTING

| | |
|-----------------------------|--------------------------|
| Fitting type | Medium rectangular plate |
| Plate length | 137 mm |
| Plate width | 115 mm |
| Plate hole length (Minimum) | 75 mm |
| Plate hole length (Maximum) | 80 mm |
| Plate hole width (Minimum) | 75 mm |
| Plate hole width (Maximum) | 105 mm |
| Plate hole diameter | 11 mm |

ALPHA

3478UOJ160P63

EAN 4031582307085
Order number 00027861



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

