PRODUCT INFORMATION

# AGILA STAINLESS

7477PJO150P51

EAN 4031582350500



Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement Noise | ●●●○○ |
| Attrition | ●●●○○ |
| Corrosion Resistance | ●●●●● |

## CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Agila stainless |
| Type | Swivel castor with total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 100 kg |
| Electric Conductive | No |
| Stainless | Yes |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall Height | 183 mm |
| Overall weight | 0.95 kg |

## HOUSING

| | |
|---|---|
| Housing Material | Stainless steel, medium |
| Fork shape | Broad |
| Swivel Bearing | Two ball races |
| Housing Color | Stainless steel |
| Offset | 36 mm |
| Swivel interference | 262 mm |

## WHEEL

| | |
|---|---|
| Body material | Polypropylene |
| Tread Material Mix | Thermoplastic rubber |
| Bearing | Plain bearing |
| Threadguards | Without threadguard |
| Diameter | 150 mm |
| Tread width | 32 mm |
| Hardness of tread (A) | 87 Shore A |

## FITTING

| | |
|---|---|
| Fitting type | Rectangular plate |
| Plate length | 95 mm |
| Plate width | 70 mm |
| Plate hole length (Maximum) | 75 mm |
| Plate hole width (Maximum) | 50 mm |
| Plate hole diameter | 11 mm |

© Copyright 2026 TENTE International GmbH


# AGILA STAINLESS


7477PJO150P51


EAN 4031582350500


BETTER MOBILITY. BETTER LIFE.

## Product Drawings






© Copyright 2026 TENTE International GmbH