

AGILA STAINLESS

7470PJO050P30-11

EAN 4031582350920



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ● ●

CORE ATTRIBUTES

Product Name	Agila stainless
CO2 emission (scope 3)	0.57
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	Yes
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	69 mm
Overall width	43 mm
Overall weight	0.15 kg

HOUSING

Housing Material	Stainless steel, medium
Fork shape	Broad
Swivel Bearing	Two ball races
Housing Color	Stainless steel
Offset	24 mm
Swivel radius	49 mm
Swivel interference	98 mm
Dome diameter	41 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing
Wheel Color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	50 mm
Tread width	19 mm
Body width	19 mm
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm
Hint	Castors can be mounted with standard screws of any length.

AGILA STAINLESS

7470PJO050P30-11

EAN 4031582350920

Order number 00036671

Product Drawings



BETTER MOBILITY. BETTER LIFE.

