PRODUCT INFORMATION

# LUMINA

## 5520PJI050L51-10 plane/~9006/9011

EAN 4031582335545

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement Noise | ●●●○○ |
| Attrition | ●●●○○ |
| Corrosion Resistance | ●●●●○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Lumina |
| Type | Swivel castor |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 3 km/h | 40 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 80 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall Height | 71.5 mm |
| Overall width | 55 mm |
| Overall weight | 0.1 kg |
| Face type | Aeroplane |

### HOUSING

| | |
|---|---|
| Housing Material | Polyamide |
| Fork shape | Twin wheel housing, closed, with dome |
| Swivel Bearing | Stem, swiveling |
| Housing Color | White aluminium (similar RAL9006) |
| Offset | 20 mm |
| Swivel radius | 66.5 mm |
| Swivel interference | 133 mm |
| Dome diameter | 23 mm |

### WHEEL

| | |
|---|---|
| Body material | Polypropylene |
| Tread Material Mix | Thermoplastic rubber |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Tread Color | Graphite black (RAL9011) |
| Wheel Color | White aluminium (similar RAL9006) |
| Threadguards | Without threadguard |
| Diameter | 50 mm |
| Tread width | 10 mm |
| Axle Hole Diameter | 0 mm |
| Hub Length | 0 mm |
| Body width | 10 mm |
| Hardness of tread (A) | 90 Shore A |

### FITTING

| | |
|---|---|
| Fitting type | Blind hole for B10 |
| Bolt hole diameter | 10 mm |

Red Dot Design Award

© Copyright 2026 TENTE International GmbH


# LUMINA


5520PJI050L51-10 plane/~9006/9011

EAN 4031582335545

Order number 00078991

**Product Drawings**



Red Dot Design Award

© Copyright 2026 TENTE International GmbH