PRODUCT INFORMATION

KAPPA LOAD

9658FTP200P64 CL97

EAN 4031582316230



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●○
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●●○

CORE ATTRIBUTES

Product name	Kappa load
Type	Fixed caster
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	3703.76 lb
Load capacity at 3.7 mph	3086.47 lb
Electric conductive	no
Stainless	no
Load capacity Static	6172.94 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall height	10.04 in
Overall width	5.51 in
Overall weight	24.51 lb

HOUSING

Housing Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
Housing Color	Zink-iron (transparent)
Lubrication nipple	1
Dome diameter	5.12 in

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	7.87 in
Tread width	3.15 in
Body width	3.15 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

FITTING

Fitting type	Rectangular plate
Plate length	6.89 in
Plate width	5.51 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Maximum)	5.51 in
Plate hole diameter	0.59 in

© Copyright 2026 TENTE International GmbH


KAPPA LOAD


9658FTP200P64 CL97

EAN 4031582316230

BETTER MOBILITY. BETTER LIFE.

Product Drawings





© Copyright 2026 TENTE International GmbH