

# ZETA

4688UOO200P63

EAN 4031582308358



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement noise	● ● ● ● ○ ○
Attrition	● ● ● ● ● ○
Corrosion resistance	● ● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Zeta
Type	Fixed caster
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1763.7 lb
Load capacity at 3.7 mph	1410.96 lb
Electric conductive	no
Stainless	no
Load capacity Static	3527.39 lb
Temperature range (Minimum)	-22 °F
Temperature range (Maximum)	176 °F
Overall height	9.45 in
Overall width	4.61 in
Overall weight	4.43 lb

## HOUSING

Housing Material	Steel sheet, very heavy
Fork shape	Broad, reinforced
Housing Color	Blue passivated

## WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	7.87 in
Tread width	1.97 in
Body width	1.97 in
Hardness of tread (D)	75 Shore D

## FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.61 in
Plate hole length (Minimum)	2.95 in
Plate hole length (Maximum)	3.15 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.43 in

# ZETA

4688UOO200P63

EAN 4031582308358

Order number 00805413  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

