

MAXTECH

PNR400X90-Ø10 HL129 YELLOW WITH AXLE

EAN 4031582438192



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Polyurethane, foamed
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	15.75 in
Tread width	3.54 in
Axle hole diameter	0.39 in
Hub length	5.08 in

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Load capacity at 1.8 mph	319.67 lb
Load capacity Static	639.34 lb
Overall weight	6.61 lb

MAXTECH

PNR400X90-Ø10 HL129 YELLOW WITH AXLE

EAN 4031582438192



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

