

# MAXTECH

PNR400X90-Ø10 HL129 YELLOW WITH AXLE

EAN 4031582438192



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Polyurethane, foamed
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	15.75 in
Tread width	3.54 in
Axle hole diameter	0.39 in
Hub length	5.08 in

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Load capacity at 1.8 mph	319.67 lb
Load capacity Static	639.34 lb
Overall weight	6.61 lb

# MAXTECH

PNR400X90-Ø10 HL129 YELLOW WITH AXLE

EAN 4031582438192



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

