

BASETECH

POO065X30-Ø12

EAN 4031582418965



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●●●

otpornost na rdju ●●●○○

OSNOVNI ATRIBUTI

Naziv proizvoda	Basetech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	120 kg
Statički Nosivost	240 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,047 kg

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Identično sa telom Tocak
Nošenje	klizni lezaj
stitnici omotaca	Bez stražara
Prečnik	65 mm
Širina omotac	30 mm
dimenzija rupa osovina	12 mm
dužina glavcine	34,5 mm
Teškoća gazećeg omotac (D)	65 Šor D

BASETECH

POO065X30-Ø12

EAN 4031582418965



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

