

COMPACTA

1530PJO040P41

EAN 4031582425376



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

CORE ATTRIBUTES

Product name	Compacta
Type	Swivel caster
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	44.09 lb
Electric conductive	no
Stainless	no
Load capacity Static	88.18 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	2.01 in
Overall weight	0.15 lb

HOUSING

Housing Material	Steel sheet, light
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	One ball race
Offset	0.75 in
Swivel radius	1.54 in
Swivel interference	3.07 in

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Axle	Riveted
Threadguards	Without threadguard
Diameter	1.57 in
Tread width	0.91 in
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Square plate
Plate length	1.46 in
Plate width	1.46 in
Plate hole length (Maximum)	1.18 in
Plate hole width (Maximum)	1.18 in