

PRODUCT INFORMATION

SUPRATECH

PJP200x45-Ø12,2 HL60

EAN 4031582444209



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	200 mm
Tread width	45 mm
Axle Hole Diameter	12 mm
Hub Length	60 mm
Hardness of tread (A)	65 Shore A

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Supratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	250 kg
Electric Conductive	No
Stainless	No
Load capacity Static	500 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.24 kg

SUPRATECH

PJP200x45-Ø12,2 HL60

EAN 4031582444209



BETTER MOBILITY. BETTER LIFE.

Product Drawings

