

# SUPRATECH

PJO050x18-Ø8

EAN 4031582428353



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	50 mm
Tread width	18 mm
Axle Hole Diameter	8 mm
Hub Length	21 mm
Hardness of tread (A)	87 Shore A

## PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement Noise	● ● ● ● ○ ○
Attrition	● ● ● ● ○ ○
Corrosion Resistance	● ● ● ● ○ ○

## CORE ATTRIBUTES

Product Name	Supratech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	35 kg
Electric Conductive	No
Stainless	No
Load capacity Static	70 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.02 kg

# SUPRATECH

PJO050x18-Ø8

EAN 4031582428353



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

