

LINEA LIGHT

5920UAP065L51-10 RAL 9002

EAN 4031582437065



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Linea light
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	90 kg
Load capacity Static	180 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	68 mm
Overall width	46 mm
Overall weight	0.118 kg

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	65 mm
Tread width	13.9 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	56 mm
Swivel interference	112 mm
Dome diameter	23 mm

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	10 mm



Deutscher
Designer
Club



Interzum
Award



IF
Design
Award

LINEA LIGHT

5920UAP065L51-10 RAL 9002

EAN 4031582437065



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

