

# NOVATECH

ETP085X90-Ø17 HL90

EAN 4031582369465



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	Čelik, gvožđe
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	85 mm
Širina omotac	90 mm
dimenzija rupa osovina	17 mm
duzina glavčine	90 mm
Teškoća gazećeg omotac (A)	92 Šor A
Tip ležaja	6303

## PERFORMANSE

Performanse kotrljanja ● ● ● ● ○

Buka u pokretu ● ● ● ○ ○

Ishrana ● ● ● ● ○

otpornost na rdju ● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda Novatech

Tip Tocak

Nosivost na 3 km/h 800 kg

Statički Nosivost 1600 kg

Temperaturni opseg (Minimalno) -20 °C

Opseg temperature (maksimalni) 60 °C

## TEHNIČKI CRTEŽI

