

ALPHA

3478PJO080P62 TFR

EAN 4031582397802



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Alpha |
| Housing type | Fixed castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 70 kg |
| Load capacity Static | 140 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 108 mm |
| Overall weight | 0.453 kg |

WHEEL

| | |
|-----------------------|----------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Plain bearing |
| Axle | Screwed with nut |
| Threadguards | Without threadguard |
| Diameter | 80 mm |
| Tread width | 28 mm |
| Hardness of tread (A) | 87 Shore A |

HOUSING

| | |
|---------------|--------------------|
| Material fork | Steel sheet, heavy |
| Fork shape | Broad |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 103 mm |
| Plate width | 85 mm |
| Plate hole length (Minimum) | 77 mm |
| Plate hole length (Maximum) | 80 mm |
| Plate hole width (Maximum) | 60 mm |
| Plate hole diameter | 9 mm |

ALPHA

3478PJO080P62 TFR

EAN 4031582397802



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

