

ELASTECH

JFC150X32-Ø8

EAN 4031582319958
Broj porudžbine 00024889

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Cink die-cast
	mekan
materijal omotaca	Elastična guma, neobeležena, vulkanizovana
Nošenje	precizini kuglični lezaj, nerdjajuci
stitnici omotaca	Sa threadguard
Prečnik	150 mm
Širina omotac	32 mm
dimenzija rupa osovina	8 mm
duzina glavcine	35,5 mm
Teškoća gazećeg omotac (A)	75 Šor A

PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●○○

otpornost na rdju ●●●○○

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Tip	Tocak
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	150 kg
Statički Nosivost	300 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	0,926 kg

ELASTECH

JFC150X32-Ø8

EAN 4031582319958
Broj porudžbine 00024889



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

