

BASETECH

POO080X34-Ø12

EAN 4031582418972



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Identično sa telom Tocak
Nošenje	klizni lezaj
stitnici omotaca	Bez stražara
Prečnik	80 mm
Širina omotac	34 mm
dimenzija rupa osovina	12 mm
dužina glavnice	44,4 mm
Teškoća gazećeg omotac (D)	65 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Basetech
Tip kućišta	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	125 kg
Statički Nosivost	250 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,064 kg

BASETECH

POO080X34-Ø12

EAN 4031582418972



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

