

ELASTECH

IEP 300X55-Ø25 HL60

EAN 4031582319774
Order number 00837180



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Aluminium
Tread hardness	soft
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Wheel color	Jet black (similar RAL9005)
Threadguards	Without threadguard
Diameter	300 mm
Tread width	55 mm
Axle hole diameter	25 mm
Hub length	60 mm
Body width	55 mm
Hardness of tread (A)	68 Shore A

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	600 kg
Load capacity at 6 km/h	480 kg
Load capacity Static	1200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall weight	3.865 kg

ELASTECH

IEP 300X55-Ø25 HL60

EAN 4031582319774
Order number 00837180



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

