

AGILA

2470DIK125R07-19/21,5

EAN 4031582328318
Order number 00006668



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	165 mm
Overall width	60 mm
Overall weight	1.161 kg

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Cone ball bearing
Wheel color	Blue passivated
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Body width	32 mm
Hardness of tread (A)	80 Shore A

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Colour	Blue passivated
Offset	41 mm
Swivel radius	103.5 mm
Swivel interference	207 mm
Dome diameter	60 mm

FITTING

Fitting type	Synthetic expander, round
Stem length	22 mm
Expander fitting (Minimum)	19 mm
Expander fitting (Maximum)	22 mm
Hint	Please indicate required tube innerdiameter when ordering.

AGILA

2470DIK125R07-19/21,5

EAN 4031582328318
Order number 00006668



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

