

PRODUCT INFORMATION

DURATECH

UOP250x50-Ø20 TFR

EAN 4031582390650



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide |
| Tread Material Mix | Identical with wheel body |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 250 mm |
| Tread width | 50 mm |
| Axle Hole Diameter | 20 mm |
| Hub Length | 60 mm |
| Hardness of tread (D) | 75 Shore D |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll Performance | ● ● ● ● ● |
| Movement Noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ● |
| Corrosion Resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product Name | Duratech |
| Type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 1000 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 2000 kg |
| Temperature range (Minimum) | -30 °C |
| Temperature range (Maximum) | 80 °C |
| Overall weight | 1.42 kg |

DURATECH

UOP250x50-Ø20 TFR

EAN 4031582390650



BETTER MOBILITY. BETTER LIFE.

Product Drawings

