PRODUCT INFORMATION

DURATECH

UOP250x50-Ø20 TFR

EAN 4031582390650



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread Material Mix	Identical with wheel body
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	250 mm
Tread width	50 mm
Axle Hole Diameter	20 mm
Hub Length	60 mm
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll Performance	●●●●●
Movement Noise	●●●○○
Attrition	●●●●●
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Duratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	1000 kg
Electric Conductive	No
Stainless	No
Load capacity Static	2000 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	80 °C
Overall weight	1.42 kg

© Copyright 2026 TENTE International GmbH


DURATECH

UOP250x50-Ø20 TFR

EAN 4031582390650

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH