

# ELASTECH

JFC150X32-Ø8

EAN 4031582319958  
Order number 00024889



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Zinc die-cast
Tread hardness	soft
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, stainless
Threadguards	With threadguard
Diameter	150 mm
Tread width	32 mm
Axle hole diameter	8 mm
Hub length	35.5 mm
Hardness of tread (A)	75 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	150 kg
Load capacity Static	300 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall weight	0.926 kg

# ELASTECH

JFC150X32-Ø8

EAN 4031582319958  
Order number 00024889



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

