

PRODUCT INFORMATION

PURETECH AIR

DPP400x100-Ø25 HL74 2PR

EAN 4031582317831



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Puretech air
Type	Wheel
Load capacity at 3 km/h	200 kg
Electric Conductive	No
Stainless	No
Load capacity Static	400 kg
Overall weight	2.45 kg

WHEEL

Tread hardness	soft
Body material	Sheet Steel
Tread Material Mix	Pneumatic tyre, line profile
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	400 mm
Tread width	100 mm
Axle Hole Diameter	25 mm
Hub Length	74 mm
Hardness of tread (A)	55 Shore A

PURETECH AIR

DPP400x100-Ø25 HL74 2PR

EAN 4031582317831



BETTER MOBILITY. BETTER LIFE.

Product Drawings

