

# NOVATECH

ETP095X40-Ø20 HL45

EAN 4031582330403



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	95 mm
Tread width	40 mm
Axle hole diameter	20 mm
Hub length	45 mm
Hardness of tread (A)	92 Shore A
Bearing type	6204ZV

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Housing type	Wheel
Load capacity at 3 km/h	400 kg
Load capacity Static	800 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	1.585 kg

## TECHNICAL DRAWINGS

