

STORA

2875QMP125P30-13

EAN 4031582302455



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Stora
Type	Swivel castor with wheel brake
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	80 kg
Electric Conductive	No
Stainless	No
Load capacity Static	160 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	60 °C
Overall Height	153 mm
Overall width	74 mm
Overall weight	0.72 kg

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Special Function
Swivel Bearing	Two ball races
Housing Color	Blue passivated
Offset	40 mm
Swivel radius	102.5 mm
Swivel interference	205 mm
Dome diameter	65 mm

WHEEL

Body material	Polyurethane injected
Tread Material Mix	Double flanged with tracks
Bearing	Precision ball bearing
Wheel Color	Slate grey (RAL7015)
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Body width	32 mm
Hardness of tread (D)	59 Shore D

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

STORA

2875QMP125P30-13

EAN 4031582302455

Order number 00034015

Product Drawings



BETTER MOBILITY. BETTER LIFE.

