

LINEA LOW HEIGHT

5940UAP075P30-10 LH 9002/7015/9002

EAN 4031582370768



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ● ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Linea low height
Emisija CO2 (obuhvat 3)	1.18
Tip	Okretanje Tocak
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	90 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	180 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	78 mm
Ukupna širina	58 mm
Ukupna težina	0.21 kg

KUCISTE

Materijal kućišta	poliamid
oblik viljuska	kuciste za dva Tocak
okretni lezaj	precizini kuglicni lezaj
Boja	Siva bela (RAL9002)
ofset	23 mm
okretni radijus	60.5 mm
Otpor okretanju	121 mm
Prečnik kupole	30 mm

TOCAK

Materijal za telo	poliamid
materijal omotaca	Poliuretan, liveno
Nošenje	precizini kuglicni lezaj
Boja omotac	Slat siva (RAL7015)
Boja Tocak	Slat siva (RAL7015)
stitnici omotaca	Sa threadguard
Prečnik	75 mm
Širina omotac	15 mm
dimenzija rupa osovina	0 mm
duzina glavine	0 mm
Širina tela	15 mm
Teškoća gazećeg omotac (A)	92 Šor A

PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	10 mm

Deutscher
dizajner
ClubInterzum
nagradaproduct
design
awardIF
nagrada
za Dizajn

LINEA LOW HEIGHT


5940UAP075P30-10 LH 9002/7015/9002

EAN 4031582370768

Broj porudžbine 00770588
Crteži proizvoda



BETTER MOBILITY. BETTER LIFE.



Deutscher
dizajner
Club



Interzum
nagrada



product
design
award

IF
nagrada
za Dizajn