

ALPHA STAINLESS

8470UAD100P30-11 RED

EAN 4031582370072



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	●●●○○
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●●●

CORE ATTRIBUTES

Product name	Alpha stainless
Housing type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	330.69 lb
Load capacity Static	661.39 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall height	5.04 in
Overall weight	1.77 lb

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Roller bearing, stainless
Axle	Screwed with nut
Diameter	3.94 in
Tread width	1.26 in
Hardness of tread (D)	42 Shore D

HOUSING

Material	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	1.61 in
Swivel radius	3.58 in
Swivel interference	7.17 in
Stainless	✓

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.43 in

ALPHA STAINLESS

8470UAD100P30-11 RED

EAN 4031582370072



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

