

PRODUCT INFORMATION

# NOVATECH

RK.ETP075x60-Ø47x14

EAN 4031582369502



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### WHEEL

|                       |                     |
|-----------------------|---------------------|
| Body material         | Undefined           |
| Tread Material Mix    | Polypropylene, soft |
| Diameter              | 75 mm               |
| Tread width           | 60 mm               |
| Hardness of tread (A) | 92 Shore A          |
| Ball bearing diameter | 47 mm               |
| Ball bearing width    | 14 mm               |

### PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

### CORE ATTRIBUTES

|                             |          |
|-----------------------------|----------|
| Product Name                | Novatech |
| Type                        | Wheel    |
| Load capacity at 3 km/h     | 550 kg   |
| Electric Conductive         | No       |
| Stainless                   | No       |
| Load capacity Static        | 1100 kg  |
| Temperature range (Minimum) | -20 °C   |
| Temperature range (Maximum) | 60 °C    |

Product Drawings

