PRODUCT INFORMATION

# DURATECH

## TOP 082x80-Ø20 HL82

EAN 4031582322606



Image may differ from the original product

### WHEEL

| | |
|---|---|
| Body material | Polyamide, heavy |
| Tread Material Mix | Identical with wheel body |
| Bearing | Precision ball bearing |
| Wheel Color | Natural white |
| Threadguards | Without threadguard |
| Diameter | 82 mm |
| Tread width | 80 mm |
| Axle Hole Diameter | 20 mm |
| Hub Length | 82 mm |
| Body width | 80 mm |
| Hardness of tread (D) | 75 Shore D |
| Bearing type | 6204ZV |

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●●● |
| Movement Noise | ●●○○○ |
| Attrition | ●●●●● |
| Corrosion Resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Duratech |
| Type | Wheel |
| Standard | EN12533 - Heavy Duty Castors |
| Load capacity at 4 km/h | 750 kg |
| Load capacity at 6 km/h | 600 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 1500 kg |
| Temperature range (Minimum) | -40 °C |
| Temperature range (Maximum) | 80 °C |
| Overall weight | 0.51 kg |

© Copyright 2026 TENTE International GmbH

# DURATECH

## TOP 082x80-Ø20 HL82

EAN 4031582322606

Order number 00802945

**Product Drawings**







