

PURETECH

PVR 080x35-Ø12 HL44,4

EAN 4031582321241



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ● ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	70 kg
Električni provod	no
nerdjajući	no
Statički Nosivost	140 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0.16 kg

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma crna
Nošenje	kotrljajući lezaj
Boja Tocak	Grafitna crna (RAL9011)
stitnici omotaca	Bez stražara
Prečnik	80 mm
Širina omotac	35 mm
dimenzija rupa osovina	12 mm
dužina glavnice	44.4 mm
Širina tela	35 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

PURETECH

PVR 080x35-Ø12 HL44,4

EAN 4031582321241

Broj porudžbine 00004985
Product Drawings



BETTER MOBILITY. BETTER LIFE.

