PRODUCT INFORMATION

DURATECH

MOP 100x50-Ø20

EAN 4031582320008



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●●
Movement noise	●●○○○
Attrition	●●●●●
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	3703.76 lb
Load capacity at 3.7 mph	3086.47 lb
Electric conductive	no
Stainless	no
Load capacity Static	6172.94 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	1.55 lb

WHEEL

Body material	Polyamide, super heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (D)	75 Shore D
Bearing type	6304

© Copyright 2026 TENTE International GmbH


DURATECH

MOP 100x50-Ø20

EAN 4031582320008

Order number 00801258

Product Drawings




© Copyright 2026 TENTE International GmbH

DURATECH

MOP 100x50-Ø20

EAN 4031582320003

Order number 00801258



BETTER MOBILITY. BETTER LIFE.

© Copyright 2026 TENTE International GmbH