

AGILA LIGHT

1470PA0075P40 TENTE

EAN 4031582331486
Order number 00900424



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila light
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	60 kg
Load capacity Static	120 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	100 mm
Overall width	44 mm
Overall weight	0.265 kg

WHEEL

Body material	Polypropylene
Tread material	Polyurethane, injected
Bearing	Plain bearing
Wheel color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	75 mm
Tread width	25 mm
Body width	25 mm
Hardness of tread (A)	91 Shore A
Hardness of tread (D)	40 Shore D

HOUSING

Material fork	Steel sheet, light
Fork shape	Broad
Swivel bearing	Two ball races
Colour	Blue passivated
Offset	25 mm
Swivel radius	62.5 mm
Swivel interference	125 mm
Dome diameter	41 mm

FITTING

Fitting type	Square plate
Plate length	60 mm
Plate width	60 mm
Plate hole length (Minimum)	38 mm
Plate hole length (Maximum)	48 mm
Plate hole width (Minimum)	38 mm
Plate hole width (Maximum)	48 mm
Plate hole diameter	6.3 mm

AGILA LIGHT

1470PAO075P40 TENTE

EAN 4031582331486
Order number 00900424



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

