

AGILA TWIN

2970UAH050P30-11

EAN 4031582413748



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Agila twin |
| Type | Swivel castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 70 kg |
| Load capacity Static | 140 kg |
| Temperature range (Minimum) | -40 °C |
| Temperature range (Maximum) | 80 °C |
| Overall height | 69 mm |
| Overall width | 53 mm |
| Overall weight | 0.25 kg |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Plain bearing |
| Threadguards | With threadguard |
| Diameter | 50 mm |
| Tread width | 19 mm |
| Hardness of tread (D) | 40 Shore D |

HOUSING

| | |
|---------------------|---------------------|
| Material fork | Steel sheet, medium |
| Fork shape | Twin wheel housing |
| Swivel bearing | Two ball races |
| Offset | 25 mm |
| Swivel radius | 54 mm |
| Swivel interference | 108 mm |

FITTING

| | |
|--------------------|-----------|
| Fitting type | Bolt hole |
| Bolt hole diameter | 11 mm |

AGILA TWIN

2970UAH050P30-11

EAN 4031582413748



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

