

# STEM

S70-10X25 / 11 DRILLED STEM

EAN 4031582411911



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Corrosion resistance ● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Stem
Type	Accessory
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Overall height	6 mm
Overall weight	0.051 kg

## FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	10 mm
Stem length	25 mm